

LightPath 354140 | 2.4mm Dia., 0.58 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-614** **5 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **SS\$100⁰²**

ADD TO CART

Volume Pricing	
Qty 1-10	SS\$100.82 each
Qty 11-49	SS\$89.61 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

354140 Lightpath Lens Code:

Type:

Aspheric Lens

Typical Applications:

Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
2.40 ±0.015

Clear Aperture CA (mm):
1.6

Edge Thickness ET (mm):
0.48

Center Thickness CT (mm):
1.02 ±0.03

Bevel:
Protective as needed

Optical Properties

Effective Focal Length EFL (mm):
1.45 @ 780nm

Numerical Aperture NA:
0.58

Substrate:
[D-ZK3](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
780

Coating:
BBAR (600-1050nm)

Coating Specification:
 $R_{\text{abs}} < 1.0\%$ @ 600 - 1050nm

Surface Quality:
40-20

f#:
0.86

Wavelength Range (nm):
600 - 1050

Working Distance (mm):
0.81

Conjugate Distance:
Infinite

Transmitted Wavefront Error (λ , RMS):
< 0.07

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)


Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



TECHNICAL INFORMATION

