

[See all 77 Products in Family](#)

LightPath 354330 | 6.33mm Dia., 0.68 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-165** **20+ In Stock**

[Other Coating Options](#)

-

1

+

S\$119⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$119.00 each
Qty 11-49	S\$107.10 each
Need More?	Request Quote

Product Downloads

General

354330

Lightpath Lens Code:

Aspheric Lens

Type:

Collimate or Focus Laser Light

Typical Applications:

Physical & Mechanical Properties

6.33 ±0.020	Diameter (mm):
5	Clear Aperture CA (mm):
1.56	Edge Thickness ET (mm):
3.21 ±0.03	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties

3.10 @ 830nm	Effective Focal Length EFL (mm):
0.68	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
830	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:
R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:
0.74	f/#:
350 - 700	Wavelength Range (nm):
1.8	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.20	Transmitted Wavefront Error (λ, RMS):

Environmental & Durability Factors


≤200	Operating Temperature (°C):
------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Eliminate Spherical Aberration
 - Multiple Coating Options Available
 - Range of Numerical Apertures
- LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;