

[See all 16 Products in Family](#)

TECHSPEC® 0.9X CobaltTL Telecentric Lens



0.9X Magnification



Stock **#62-901** **6 In Stock**

1 **\$2,909⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	\$2,909.00 each
Need More?	Request Quote

Product Downloads

General

CobaltTL Series **Product Family:**

Stock No. of Mounting Clamp:
[#56-025](#) Sold Separately

Telecentric Lens **Type:**

Physical & Mechanical Properties

199.80	Length (mm):
65.0	Maximum Diameter (mm):
862	Weight (g):
17.5	Flange Distance (mm):

Optical Properties

15.65mm	Horizontal Field of View, 1.1" Sensor:
14.23mm	Horizontal Field of View, 1" Sensor:
9.78mm	Horizontal Field of View, 2/3" Sensor:
8.00mm	Horizontal Field of View, 1/1.8" Sensor:
7.12mm	Horizontal Field of View, 1/2" Sensor:
17.60	Maximum Image Circle (mm):
0.075	Numerical Aperture NA, Object Side:
10 (7)	Number of Elements (Groups):
<0.089	Typical Telecentricity @ 588nm (°):
<0.014	Typical Distortion @ 588nm (%):
0.9X	Primary Magnification PMAG:
0.90	Telecentric Lens Magnification:
111	Working Distance (mm):
15.8 x 11.6	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/22	Aperture (f/#):
425 - 675nm BBAR	Coating:
±0.33mm at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.9X	Magnification:
VIS	Lens Wavelength Range:

Sensor

1.1"	Maximum Sensor Format:
2.20	Pixel Size (µm):

Threading & Mounting

M62 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:

Regulatory Compliance


View	Certificate of Conformance:
----------------------	-----------------------------

Product Details


- High Resolution Bi-Telecentric Lens with In-Line Illumination Options
- Up to 20 MegaPixels, 2.2µm Pixel Size
- 1.1", C-Mount Telecentric Lens with f/#s as Low as f/4

TECHSPEC® CobaltTL Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. These telecentric lenses achieve high light throughput with industry leading low f/#s. Featuring less than 0.015° telecentricity and low 0.013% distortion, these lenses are ideal for image stitching applications. These 17.6mm diagonal sensor format lenses are compatible with the Sony IMX304 1.1" sensors and other similar format sensors such as the Sony IMX183. TECHSPEC® CobaltTL Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. In-line versions provide the ability to rotate/reposition the inline illumination port to allow for maximum flexibility when machine building. TECHSPEC® CobaltTL Telecentric Lenses are compatible with high vibration environments and feature a removable recessed set screw for securely locking the iris in place.


Technical Information




#62-901, 0.9X CobaltTL Telecentric Lens, Distortion Plot




#62-901, 0.9X CobaltTL Telecentric Lens, Relative Illumination Plot




#62-901, 0.9X CobaltTL Telecentric Lens, Telecentricity Plot




#62-901, 0.9X CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 111mm Working Distance, f6



#62-901, 0.9X CobaltTL Telecentric Lens, Depth of Field Plot, 111mm Working Distance, f6



#62-901, 0.9X CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 111mm Working Distance, f10



#62-901, 0.9X CobaltTL Telecentric Lens, Depth of Field Plot, 111mm Working Distance, f10

Description		Stock No.	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-921	197.59mm	138.6mm	50mm
0.36X	C-Mount	#88-602	163.5mm	70mm	43.5mm
0.5X	C-Mount	#62-911	172.9mm	90mm	50mm
0.55X	C-Mount	#88-603	182.5mm	62mm	43.5mm
0.69X	C-Mount	#15-872 / #15-873 (In-Line)	174.96mm	55mm	46mm
0.9X	C-Mount	#62-901	199.8mm	65mm	53mm