

TECHSPEC[®] 0° AOI, 12.5mm Square, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-434** 20+ In Stock

-

1

+

S\$70⁷⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$70.70 each
Qty 10-25	S\$63.70 each
Qty 26-49	S\$60.55 each
Need More?	Request Quote

Product Downloads

General	
Cold Mirror	Type:
Physical & Mechanical Properties	
1.10 ±0.2	Thickness (mm):
12.5 x 12.5	Dimensions (mm):

Dimensional Tolerance (mm):	
+0.0/-0.2	
Length (mm):	
12.50	
Width (mm):	
12.50	
Optical Properties	
Transmission (%):	
Longpass Filter	
Coating Type:	
Dielectric	
Coating:	
Cold Mirror, 0°	
Surface Flatness (P-V):	
4 - 6λ	
Wavelength Range (nm):	
400 - 1150	
Substrate: ☐	
BOROFLOAT®	
Angle of Incidence (°):	
0	
Coating Specification:	
R _{avg} ≥95% @400 - 690nm and T _{avg} ≥90% @ 750 - 1200nm	
AR Coating: R _{avg} <1% @ 700 - 1150nm	
Surface Quality:	
80-50	


Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	



Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information





Quote Your Size

Compatible Mounts

;