

TECHSPEC[®] 0° AOI, 20.0mm Square, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock **#64-456** 20+ In Stock

-

1

+

S\$76³⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$76.30 each
Qty 10-25	S\$68.95 each
Qty 26-49	S\$65.45 each
Need More?	Request Quote

Product Downloads


General	
Shortpass Filter	Type:
Physical & Mechanical Properties	
20.0 x20.0	Dimensions (mm):
1.10 ±0.2	Thickness (mm):

+0.0/-0.2	
Dimensional Tolerance (mm):	
Optical Properties	
0	Angle of Incidence (°):
Hot Mirror, 0°	Coating:
BOROFLOAT®	Substrate: ☐
80-50	Surface Quality:
Coating Specification: T _{avg} >90% @ 400 - 690nm, R _{avg} >95% @ 710 - 1150nm AR: R _{avg} <1% @ 400 - 700nm	
400 - 1150	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
Dielectric	Coating Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- High Transmission from 400 - 690nm
 - High Reflection from 750 - 1125nm
 - Ideal for Minimizing Heat Build-Up
- TECHSPEC® High Performance Hot Mirrors feature a multi-layer dielectric coating optimized for greater than 85% transmission of visible light and greater than 95% reflection of IR wavelengths. For high power illumination, forced air cooling is recommended. Hot mirrors, also known as heat-reflecting mirrors, are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. TECHSPEC High Performance Hot Mirrors are ideal for minimizing heat build-up. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major attributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

Technical Information



Quote Your Size

Compatible Mounts