

TECHSPEC® 10" Diameter x 60" FL Protected Aluminum, Parabolic Mirror



Stock **#32-274-522** [CONTACT US](#)

- 1 + **\$S\$3,221.90**

ADD TO CART

Qty 1-2
\$S\$3,221.90
Qty 3+
\$S\$2,739.05
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ [BOROFLOAT®](#) [SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 10.0 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 60.0
Effective Focal Length EFL (mm): 1,524.00
Radius of Curvature (mm): 3,048.00
Aperture (f/#): f/6
Coating: Protected Aluminum (400-2000nm)
Coating Specification: Ravg >85% @ 400 - 700nm Ravg >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant