

[See all 33 Products in Family](#)

10 x 10mm, 250µm Pitch, 6° Div., Cyl. Microlens Array UV-VIS



Stock #72-598 [CONTACT US](#)

⊖ 1 ⊕ **\$\$1,311⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-10	\$\$1,311.00 each
Qty 11-25	\$\$1,053.00 each
Qty 26-49	\$\$983.00 each
Need More?	Request Quote

Product Downloads

General

Lens Array **Type:**

Physical & Mechanical Properties

10.0 x 10.0 ±0.05 **Dimensions (mm):**

0.711 **Radius R (mm):**

1.20 ±0.05 **Thickness (mm):**

Optical Properties

1.60 **Effective Focal Length EFL (mm):**

Fused Silica (Corning 7980) **Substrate:** □

UV-NIR (250-700nm) **Coating:**

250 - 700 **Wavelength Range (nm):**

Coating Specification:
R_{abs} ≤1.0% from 350 - 450nm @ 0° AOI
R_{avg} ≤1.5% @ 250 - 700nm @ 0°

±6 **Divergence Angle (°):**

250.00 ±0.25 **Pitch (µm):**

Single-Sided **Array Type:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 250:**

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.