

[See all 33 Products in Family](#)

10 x 10mm, 300µm Pitch, 1.1° Div., Cyl. Microlens Array VIS-NIR



Stock #72-587 **5 In Stock**

S\$1,311⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$1,311.00 each
Qty 11-25	S\$1,053.00 each
Qty 26-49	S\$983.00 each
Need More?	Request Quote

Product Downloads

General

Lens Array Type:

Physical & Mechanical Properties

10.0 x 10.0 ±0.05 Dimensions (mm):

3.600 Radius R (mm):

Thickness (mm):
1.20 ±0.05

Optical Properties

Effective Focal Length EFL (mm):
8.00

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
VIS-NIR (400-1000nm)

Wavelength Range (nm):
400 - 1000

Coating Specification:
R_{abs} ≤0.25% @ 880nm @ 0° AOI
R_{avg} ≤1.25% @ 400 - 870nm @ 0° AOI
R_{avg} ≤1.25% @ 890 - 1000nm @ 0° AOI

Divergence Angle (°):
±1.1

Pitch (µm):
300.00 ±0.25

Array Type:
Single-Sided

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.

Coating Curves