

10 x 10mm, 500µm Pitch, 3.2° Divergence, Cyl. Microlens Array



Stock #86-844 3-5 DAYS

- 1 + **S\$1,022.25**

ADD TO CART

Qty 1-10
S\$1,022.25
Qty 11+
S\$899.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
4.50

Substrate: [Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:
Lens Array

Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±3.2
Pitch (µm): 500.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 2.040
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.05

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View