

[See all 20 Products in Family](#)

## 100mm Low Noise BNC to BNC Cable



Stock **#90-644** NEW [CONTACT US](#)

- 1 + **S\$231<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>S\$231.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Hardware & Interface Connectivity

**Connector:**  
BNC / BNC

**Length of Cable (m):**  
0.1

### Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Ultra-Wide Adjustable Transimpedance Gain from  $10^2$  to  $10^{11}$  V/W
- Exceptional Low-Noise, High-Sensitivity Single-Beam Detection
- Optimized for Absolute Optical Power Measurements
- Designed for Direct, Alignment-Free Integration

Variable Gain Photoreceivers feature an ultra-wide adjustable transimpedance gain from  $10^2$  to  $10^{11}$  V/W, enabling precise measurement of optical signals across a broad power range. Engineered for ultra-low noise performance, these photoreceivers achieve noise equivalent power (NEP) as low as  $6\text{fW}/\sqrt{\text{Hz}}$ , ensuring accurate detection of extremely weak optical signals. Designed for single-beam detection, they provide maximum sensitivity and dynamic range, allowing for simple, alignment-free integration into optical systems. Variable Gain Photoreceivers are ideal for applications such as photonics research, optical communication testing, and precision low-light measurements.

**Note:** Power supply sold separately. Please see specifications for more details.

---