

101 x 127mm, Extended Hot Mirror



Extended Hot Mirrors

Stock **#47-304** 13 In Stock

-

1

+

S\$404⁷⁴

ADD TO CART

Volume Pricing	
Qty 1-9	S\$404.74 each
Qty 10-25	S\$364.41 each
Qty 26-49	S\$346.49 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Shortpass Filter

Type:

Physical & Mechanical Properties

101.0 x 127.0	Dimensions (mm):
3.30 ±0.2	Thickness (mm):
±0.5	Dimensional Tolerance (mm):
≥85	Clear Aperture (%):
Seamed	Edges:
Optical Properties	
0.00	Angle of Incidence (°):
Hot Mirror, 0°	Coating:
BOROFLOAT®	Substrate: □
80-50	Surface Quality:
R _{avg} ≥90% @ 750 - 1150nm R _{avg} ≥80% @ 1200 - 1600nm T _{avg} ≥85% @ 425 - 675nm	Coating Specification:
425 - 1600	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
Dielectric	Coating Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


PRODUCT DETAILS


- Improved NIR Reflectance Over Standard Hot Mirrors
- Operating Temperatures up to 230°C
- Neutral Color for 5500K or 3200K Sources to ±250K

Extended Hot Mirrors are designed to reduce the heat in an optical system without sacrificing the system's visible output. While typical hot mirrors reflect from 750nm to approximately 1250nm, Extended Hot Mirrors further reduce heat by extending the reflection range to approximately 1750nm.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major attributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

TECHNICAL INFORMATION





QUOTE YOUR SIZE

COMPATIBLE MOUNTS