


[See all 4 Products in Family](#)

**TECHSPEC® 1030nm, 25.4mm Dia., 45° Thin Film Polarizer**



TECHSPEC® Ultrafast Thin Film Polarizers

Stock **#12-992** **4 In Stock**

⊖ 1 ⊕ **\$651<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-4	<b>\$651.00</b> each
Qty 5-9	<b>\$582.40</b> each
Qty 10+	<b>\$522.20</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

**Physical & Mechanical Properties**

25.40 +0.00/-0.10 **Diameter (mm):**

3.00 ±0.10 **Thickness (mm):**

Parallelism (arcmin):

<3

Clear Aperture (%):

85

## Optical Properties

Angle of Incidence (°):

45 ±1

Coating:

Thin Film Polarizer (1030nm)

Design Wavelength DWL (nm):

1030

Extinction Ratio:

1000:1

Substrate:

Fused Silica (Corning 7980)

Surface Quality:

10-5

Transmitted Wavefront, P-V:

M10 @ 633nm

Coating Specification:

S1: R<sub>s</sub> >99.8% @ 1030nm, T<sub>p</sub> >98% @ 1030nm

S2: R<sub>p</sub> <0.1% @ 1030nm

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers
- Optimized for Separation of S and P Polarizations at 45° AOI
- High Extinction Ratio of 1000:1 @DWL

TECHSPEC® Ultrafast Thin Film Polarizers utilize thin film coating technology to achieve optimal performance at 800 and 1030nm. The ion beam sputtering (IBS) coating on these polarizers provides >99.8% reflectance of the s-polarization and >98% transmission of the p-polarization at a 45° angle of incidence. TECHSPEC Ultrafast Thin Film Polarizers are ideal to use with ultrafast laser sources such as Ti:sapphire and Yb:doped lasers. Please contact us if your application requires an Ultrafast Thin Film Polarizer with a custom size or coating specifications.

**Note:** The arrow on the edge of these optics points towards the thin film polarizer coating.

## Coating Curves

;