

TECHSPEC®

1.0mm Dia. x 2.0mm FL, VIS-NIR Coated, Plano-Convex Lens



Stock **#65-292** 3-5 DAYS

[Other Coating Options](#)

- 1 +

S\$114.55

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| S\$114.55                     |
| Qty 10+                       |
| S\$102.95                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
1.00 +0.0/-0.025

Effective Focal Length EFL (mm):  
2.00 @ 587.6nm

|                                                                                                                                                     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>1.57                                                                                                          |
| <b>Coating:</b><br>VIS-NIR (400-1000nm)                                                                                                             |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-LASF9</a>                                                                               |
| <b>Surface Quality:</b><br>20-10                                                                                                                    |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                               |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                         |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                            |
| <b>Centering (arcmin):</b><br>30-45, typical                                                                                                        |
| <b>Center Thickness CT (mm):</b><br>0.80 ±0.05                                                                                                      |
| <b>Edge Thickness ET (mm):</b><br>0.72                                                                                                              |
| <b>Radius R<sub>1</sub> (mm):</b><br>1.70                                                                                                           |
| <b>Clear Aperture CA (mm):</b><br>0.5                                                                                                               |
| <b>f#:</b><br>2.00                                                                                                                                  |
| <b>Numerical Aperture NA:</b><br>0.25                                                                                                               |
| <b>Type:</b><br>Plano-Convex Lens                                                                                                                   |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                         |
| <b>Wavelength Range (nm):</b><br>400 - 1000                                                                                                         |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm <sup>2</sup> @ 532nm, 10ns                                                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |