

TECHSPEC[®] 10mm Dia. 1064nm 45°, Nd:YAG Laser Line Mirror



Nd:YAG ZERODUR Laser Line Mirrors

Stock **#26-434** 20+ In Stock

-

1

+

S\$268⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$268.80 each
Qty 6-25	S\$215.60 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

10.00 +0.00/-0.20

Diameter (mm):

>90

Clear Aperture (%):

Parallelism (arcsec):

30	
	Thickness (mm):
2.00 +/-0.2	
Optical Properties	
	Design Wavelength DWL (nm):
1064	
	Wavelength Range (nm):
1046 - 1074	
	Substrate:
ZERODUR®	
	Angle of Incidence (°):
45	
	Reflection at DWL (%):
99.8	
	Coating:
Laser Mirror (1064nm)	
	Coating Specification:
R _{abs} >99.8% @ 1064nm @ 45° AOI, R _{avg} >99.5% @ 1046 - 1074nm @ 45° AOI	
	Coating Type:
Dielectric	
	Surface Flatness (P-V):
λ/10	
	Surface Quality:
20-10	
	Damage Threshold, By Design:
20 J/cm² @ 1064nm, 20ns, 20Hz	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.5% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Nd:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Nd:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C these mirrors are ideal for applications where the optics will be exposed to fluctuating temperatures. The Nd:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Nd:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirror are an excellent fit for laboratories and integration into larger powerful laser systems