

TECHSPEC[®] 10mm Dia 0.50 NA, NIR Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#87-990** **5 In Stock**

☐ [Other Coating Options](#)

-

1

+

S\$586⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$586.60 each
Qty 6-10	S\$527.80 each
Qty 11-25	S\$492.80 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

10.00 +0.0/-0.1	
Centering (arcmin):	≤5
Clear Aperture CA (mm):	8
Edge Thickness ET (mm):	2.77
Center Thickness CT (mm):	6.00 ±0.1
Bevel:	Protective as needed
Shape of Back Surface:	Plano

Optical Properties	
Effective Focal Length EFL (mm):	10.00 @ 587.6nm
Numerical Aperture NA:	0.50
Back Focal Length BFL (mm):	5.89
Substrate: ☐	Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm):	587.6
Asphere Figure Error, RMS @ 632.8nm:	1.2λ
Coating:	NIR (600-1050nm)
Coating Specification:	R _{avg} ≤1.5% @ 600 - 1050nm
Surface Quality:	60-40
f/#:	1.00
Wavelength Range (nm):	600 - 1050
Conjugate Distance:	Infinite
Power (diopters):	100.00


Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 235:	Compliant


Product Details

- Low Coefficient of Thermal Expansion
- Precision and High Precision Options
- High Numerical Apertures to Maximize Throughput

TECHSPEC® UV Fused Silica Aspheric Lenses offer the benefits of an aspheric element combined with the manufacturing precision of state-of-the-art grinding and polishing equipment. These fused silica optics can be easily designed and integrated into complex optical systems with the available prescription data. Featuring low f/#'s, which allow for a larger aperture and thus more light gathering and focusing performance, these fused silica lenses are computer-optimized to eliminate spherical and minimize higher order aberrations. TECHSPEC® UV Fused Silica Aspheric Lenses offer a low coefficient of thermal expansion, making them ideal for applications in metrology, beam-focusing or collimating, and OEM integration. These lenses are available in a variety of coating options and are offered in sizes ranging from 10-50mm.

Technical Information





Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts