

TECHSPEC® 10mm Diameter 45° Rod Mirror Aluminum Coated



45° Rod Mirrors

Stock **#45-944** [CONTACT US](#)

⊖ 1 ⊕ **\$\$221²⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	\$\$221.20 each
Qty 6-25	\$\$198.80 each
Qty 26-49	\$\$176.40 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Rod Lens

Type:

Note:

Physical & Mechanical Properties

10.00 +0.00/-0.05 **Diameter (mm):**

15.00 **Length (mm):**

Protective as needed **Bevel:**

±0.1 **Length Tolerance (mm):**

Optical Properties

Protected Aluminum (400-700nm) **Coating:**

[N-BK7](#) **Substrate:**

40-20 **Surface Quality:**

±10 **Angle Tolerance (arcmin):**

$R_{avg} > 85\%$ @ 400 - 700nm **Coating Specification:**

90 **Ray Deviation (°):**

400 - 700 **Wavelength Range (nm):**

Metal **Coating Type:**

0.3 J/cm² @ 532nm & 1064nm, 10ns **Damage Threshold, By Design:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 219:**



[View](#) **Certificate of Conformance:**

PRODUCT DETAILS

- Protected Aluminum Coating
- Reflect Light at 90°

TECHSPEC® 45° Rod Mirrors are designed for use in a variety of laser and imaging systems. The mirrors can be used to redirect laser light at 90°. Their small diameters make them ideal for use in fiberscope/borescope applications where size is critical. TECHSPEC 45° Rod Mirrors feature polished elliptical surfaces and ground circumferences and bases. These components are available in a range of micro sizes for integration into a host of OEM applications.

TECHNICAL INFORMATION



Example Reflection
