

TECHSPEC[®] 10mm NIR, Lateral Displacement Non-Polarized Beamsplitter



Lateral Displacement Beamsplitters

Stock **#47-540** 10 In Stock

-

1

+

\$459²⁵

~~\$918.50~~

ADD TO CART

Volume Pricing	
Qty 1-5	\$918.50 \$459.25 each
Qty 6-25	\$733.31 \$366.66 each
Qty 26-99	\$670.58 \$335.29 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Non-Polarizing Beamsplitter

Type:

Type of Optics:


Non-Polarizing	
Physical & Mechanical Properties	
80.00	Clear Aperture (%):
Prism	Construction:
±0.1	Dimensional Tolerance (mm):
<2	Parallelism (arcmin):
Optical Properties	
±5	Angle Tolerance (arcsec):
10.00	Beam Separation (mm):
R _{avg} <0.5% @ 720 - 1080nm	Coating Specification:
T _p - T _s <6%	Extinction Ratio:
45.00	P-Polarization Transmission (%):
45.00	S-Polarization Reflection (%):
N-BK7	Substrate:
λ/8	Surface Flatness (P-V):
40-20	Surface Quality:
720 - 1080	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Visible and NIR Coating Options Offered
- Simplifies Benchtop Layout
- Split Incident Beam into Two Displaced Parallel Beams

TECHSPEC® Lateral Displacement Beamsplitters output two parallel beams separated by a fixed distance. The beamsplitters consist of a precision **rhomboid prism** cemented to a λ/8 **right angle prism**. The high tolerance design ensures the exiting beams are parallel to within 2 arcmin. TECHSPEC® Lateral Displacement Beamsplitters' entrance and exit faces feature a multi-layer anti-reflection (AR) coating for increased efficiency. Polarizing and non-polarizing coatings are available for these beamsplitters.

TECHNICAL INFORMATION



Size (A)	10mm	20mm
Beam Separation	10mm	20mm

