


[See all 11 Products in Family](#)

10mm Diameter Laser Diode Mirror



Stock **#43-853** 20+ In Stock

-

1

+

S\$39^{.20}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$39.20 each
Qty 11-24	S\$30.80 each
Need More?	Request Quote

Product Downloads

General

Type:

Flat Mirror

Physical & Mechanical Properties

Diameter (mm):

10.00 ±0.25

Dimensional Tolerance (mm):

±0.25

Thickness (mm):

3.00

Optical Properties	
Float Glass	Substrate: ☐
80-50	Surface Quality:
R _{abs} >97% @ 633nm	Coating Specification:
	Coating:
Dielectric Mirror (500-700nm)	Coating Type:
Dielectric	Design Wavelength DWL (nm):
633	

Environmental & Durability Factors	
ML-C-48497A	Durability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


Product Details

- Over 95% Reflectance of Visible Laser Diode Light
- Ideal for Multiple Reflection Systems
- Coating Optimized for 633nm at 45° AOI

Visible Laser Diode Mirrors are specially coated to attain maximum reflection of visible laser diodes. Optimized for 633nm at a 45° angle of incidence, these mirrors provide 97% reflectance versus only 85 - 90% for standard first surface mirrors. This reduced loss is particularly important in multiple reflection systems, where loss can significantly impact system efficiency. Visible Laser Diode Mirrors feature a float glass substrate and are ideal for multiple reflection systems.

Technical Information

Visible Laser Diode Mirror Reflectance at 45°



@ 500nm	95.0%
@ 550nm	97.0%
@ 600nm	97.5%
@ 633nm	97.0%
@ 635nm	97.0%
@ 650nm	96.5%
@ 670nm	96.0%
@ 675nm	95.0%
@ 700nm	94.5%

Quote Your Size

Compatible Mounts