

10X Objective, CFI Plan Achromatic

See More by [Nikon](#)



Stock #75-353 NEW 1 In Stock

-

1

+

S\$439⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$439.60 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	MRL00102
Compatible Tube Lens Focal Length (mm):	Focal Length: 200mm
Type:	Microscope Objective
Style:	Infinity Corrected
Manufacturer:	Nikon

Physical & Mechanical Properties	
2.2	Field of View (mm):
49.40	Length excluding Threads (mm):
27	Maximum Diameter (mm):
90	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
0.64	Horizontal Field of View, 1/2" Sensor:
0.88	Horizontal Field of View, 2/3" Sensor:
10X	Magnification:
0.25	Numerical Aperture NA:
10.5	Working Distance (mm):
22	Field Number (mm):
59.9	Parfocal Length (mm):
N/A	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M25 x0.75	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Exceptional Flat-Field Imaging
- High Numerical Apertures and Oil Immersion Options Available
- Wide Magnification Range (1Xto 100X)

Nikon’s CFI Plan Achromat Objectives deliver exceptional flat-field imaging ensuring sharp, distortion-free clarity across the entire field of view, making these objectives ideal for both visual inspection and high-precision digital imaging. With high numerical apertures and specialized oil immersion options available, these objectives offer enhanced resolution and light-gathering capability for demanding high-magnification applications. Nikon CFI Plan Achromat Objectives are available in 1Xup to 100Xmagnification, providing solutions for low-magnification overviews or detailed high-resolution imaging. Color corrected for the entire visible spectrum; these objectives are suitable for brightfield and fluorescence observation in routine lab work and photomicrography.