

[See all 33 Products in Family](#)

12 x 12mm, 500µm Pitch, 2.3° Div., Cyl. Microlens Array UV-VIS



Stock **#72-603** **1 In Stock**

⊖ 1 ⊕ **S\$1,040⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-10	S\$1,040.00 each
Qty 11-25	S\$832.00 each
Qty 26-49	S\$780.00 each
Need More?	Request Quote

Product Downloads

General

Lens Array **Type:**

Physical & Mechanical Properties

12.0 x 12.0 ±0.10 **Dimensions (mm):**

5.500 **Radius R (mm):**

2.00 ±0.10 **Thickness (mm):**

Optical Properties

Effective Focal Length EFL (mm):
12.20 @ 1064nm

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
UV-NIR (250-700nm)

Wavelength Range (nm):
250 - 700

Coating Specification:
R_{abs} ≤ 1.0% from 350 - 450nm @ 0° AOI
R_{avg} ≤ 1.5% @ 250 - 700nm @ 0°

Divergence Angle (°):
2.3 (Full Width)

Pitch (µm):
500.00

Array Type:
Single-Sided

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.