

TECHSPEC[®] 12.0mm Dia. x 48.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#32-853** 3-5 DAYS

[Other Coating Options](#)



1



S\$50.75

ADD TO CART

Qty 1-9

S\$50.75

Qty 10+

S\$45.67

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):
48.00 @ 587.6nm

Back Focal Length BFL (mm): 46.36
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.05
Edge Thickness ET (mm): 1.76
Radius R₁ (mm): 24.82
Clear Aperture CA (mm): 11
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View