

TECHSPEC® 12.0mm Diameter x -24 FL, MgF₂ Coated, Plano-Concave Lens



Stock **#45-017** 3-5 DAYS

[Other Coating Options](#)

- 1 + **S\$51.48**

ADD TO CART

Qty 1-9
S\$51.48
Qty 10+
S\$46.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-24.00

Substrate: N-BK7
f#: 2.00
Numerical Aperture NA: 0.25
Coating: MgF₂ (400-700nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -26.32
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R_{avg} ≤1.75% @ 400 - 700nm
Edge Thickness ET (mm): 4.79
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -12.40
Surface Quality: 40-20
Damage Threshold, Reference: 10 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View