

## 12.5 x 12.5mm 600 Grit Ground Glass Diffuser



Stock **#38-785** **3 In Stock**

S\$30<sup>.10</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>S\$30.10</b> each
Qty 11+	<b>S\$25.55</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Ground Glass Diffuser **Type:**

Sandblasted on first surface **Note:**

### Physical & Mechanical Properties

$\pm 0.76$  **Dimensional Tolerance (mm):**

12.50 x 12.50 **Dimensions (mm):**

Cut	<b>Edges:</b>
600	<b>Grit:</b> <input type="checkbox"/>
1.60	<b>Thickness (mm):</b>
12.50	<b>Width (mm):</b>
12.50	<b>Length (mm):</b>

## Optical Properties

Uncoated	<b>Coating:</b>
Float Glass	<b>Substrate:</b> <input type="checkbox"/>
350 - 2000	<b>Wavelength Range (nm):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



## Quote Your Size

## Compatible Mounts