

TECHSPEC® 12.5mm Dia x 10mm FL Acylinder Lens, MgF₂ Coated



TECHSPEC Acylinder Lenses

Stock **#86-034** **3 In Stock**

⊖ 1 ⊕ **\$994.00**

ADD TO CART

Volume Pricing	
Qty 1-5	\$994.00 each
Qty 6-25	\$795.20 each
Qty 26-49	\$733.60 each
Need More?	Request Quote

Product Downloads

General

Acylinder Lens

Type:

Physical & Mechanical Properties

12.50 +0.0/-0.1

Diameter (mm):

6.00

Center Thickness CT (mm):

Center Thickness Tolerance (mm):

±0.1

Clear Aperture (%):

90.00

Edge Thickness ET (mm):

2.8

Optical Properties

Effective Focal Length EFL (mm):

10.00

Substrate:

N-SF5

f/#:

0.8

Numerical Aperture NA:

0.63

Coating:

MgF₂ (400-700nm)

Wavelength Range (nm):

400 - 700

Back Focal Length BFL (mm):

6.4

Coating Specification:

R_{avg} ≤ 1.75% @ 400 - 700nm

Focal Length Specification Wavelength (nm):

587.6

Surface Accuracy, RMS (μm):

1.0

Surface Quality:

60-40

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 235:

Compliant

Product Details


- Diffraction Limited Design
- Ideal for Creating Thin Line Profiles of Monochromatic Light Sources
- Focus Light in Single Dimension

TECHSPEC® Acylinder Lenses are similar to aspheric lenses in that they provide diffraction-limited focusing performance in only one dimension. By reducing spherical aberration along the focusing axis, TECHSPEC® Acylinder Lenses are ideal for creating thin line profiles. Compared to standard cylinder lenses, TECHSPEC® Acylinder Lenses also dramatically reduce the spot size of monochromatic light sources to provide sharp, thin lines.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information



Coating Curves

