

12.5mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#27-402** 20+ In Stock

-

1

+

S\$26⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$26.60 each
Qty 6-25	S\$21.00 each
Qty 26-99	S\$19.60 each
Need More?	Request Quote

Product Downloads

General	
Flat Mirror	Type:
Physical & Mechanical Properties	
12.50 ±0.76	Diameter (mm):
1.00 Nominal	Thickness (mm):

Protective as needed		Bevel:
Optical Properties		
Metal		Coating Type:
Protected Aluminum (400-700nm)		Coating:
4 - 6λ		Surface Flatness (P-V):
400 - 700		Wavelength Range (nm):
Float Glass		Substrate: □
45.00		Angle of Incidence (°):
R _{avg} >85% @400 - 700nm		Coating Specification:
80-50		Surface Quality:

Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	


Product Details

- Wide Variety of Shapes and Sizes Available
- >85% Reflection of Visible Light
- [Contact Us](#) for Custom Sizes

4 - 6λ First Surface Mirrors are an economical choice for a wide range of applications. First surface mirrors feature high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in circular, square, and rectangular dimensions. Rectangular 4 - 6λ First Surface Mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. The mirrors have a protected aluminum coating, and they reflect greater than 85% of visible light.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts