

## 12.5mm Diameter 220 Grit Ground Glass Diffuser



Stock #62-616 **20+ In Stock**

- 1 + \$19<sup>95</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>\$19.95</b> each
Qty 11+	<b>\$18.20</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Ground Glass Diffuser **Type:**

Sandblasted on first surface **Note:**

#### Physical & Mechanical Properties

12.50 ±0.25 **Diameter (mm):**

Ground **Edges:**

220 **Grit:**

1.60 **Thickness (mm):**

## Optical Properties

Uncoated **Coating:**

Float Glass **Substrate:**

350 - 2000 **Wavelength Range (nm):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**


## Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



[Quote Your Size](#)

[Compatible Mounts](#)