

TECHSPEC® 12.5mm FL f/2.5, Blue Series M12 Lens



12.5mm FL Blue Series M12 Lens



Stock **#58-205** 3-5 DAYS

- 1 +

S\$137.00

ADD TO CART

Qty 1-49
S\$137.00
Qty 50+
S\$108.23
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
22.90

Horizontal Field of View, 1/2" Sensor:
78.0mm - 28.8°

Maximum Diameter (mm):

15
Outer Diameter (mm): 15.0
Weight (g): 5
Horizontal Field of View, 1/3" Sensor: 58.4mm - 21.8°
Maximum Image Circle (mm): 8.00
Numerical Aperture NA, Object Side: 0.0151
Horizontal Field of View @ Max Sensor Format: 78.0mm - 28.8°
Number of Elements (Groups): 5(5)
Wavelength Range (nm): 400 - 700
Horizontal Field of View, 1/2.5" Sensor: 70.6mm - 26.2°
Type: M12 Imaging Lens
Focal Length FL (mm): 12.50
Primary Magnification PMAG: 0.082X
Maximum Sensor Format: 1/2"
Working Distance (mm): 150 - ∞
Mount: M12 x 0.5 (S-Mbunt)
Aperture (f/#): f/2.5
Distortion (%): -0.36 @ Full Field
Back Focal Length BFL (mm): 10.1 - 9.7
Coating Specification: λ/4 MgF ₂ @ 550nm
Entrance Pupil Position (mm): 10.87
Horizontal Field of View, 1/4" Sensor: 43.8mm - 16.4°
Object Space Principal Plane (mm): 10.14
Image Space Principal Plane (mm): -3.01
Field of View at Max Sensor Format: Horizontal: 78.1mm - 28.9° Vertical: 58.5mm - 21.8° Diagonal: 97.7mm - 35.7°
IR Cut Filter: No
Exit Pupil Position (mm): -2.33
Lens Wavelength Range: VIS
Imaging Lens Type: High Performance M12 Lens

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View