

TECHSPEC[®] 12.5mm Dia. 2° Nom. Fused Silica Wedge Prism 1064nm Laser V-Coat



TECHSPEC Fused Silica Wedge Prisms

Stock #39-126 CLEARANCE 3-5 DAYS

-

1

+

S\$137.68

ADD TO CART

Qty 1+

S\$137.68

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
Laser V-Coat (1064nm)

Angle Tolerance (arcsec):
30

Bevel:
Protective bevel as needed

Coating Specification:
R_{abs} <0.25% @ 1064nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

0.52
Design Wavelength DWL (nm): 1064
Diameter (mm): 12.50
Image Orientation: Beam Deviation
Power (diopters): 3.49
Ray Deviation @ 355nm (°): 2.00
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Wedge Angle: 4° 11'14"
Damage Threshold, By Design: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View