

[See all 20 Products in Family](#)

**TECHSPEC® 125mm, English Micrometer Z-Stage**



TECHSPEC® Vertical Translation Stages



Stock #66-508 [CONTACT US](#)

- 1 + **\$1,638<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-2	\$1,638.00 each
Qty 3+	\$1,425.62 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

English **Type:**

**Physical & Mechanical Properties**

Linear (Z) **Type of Movement:**

**Guide System:**

Crossed Roller Bearing

125 x 125	<b>Stage Size (mm):</b>
20	<b>Travel (mm):</b>
1/4-20	<b>Center Hole:</b>
Aluminium Stage	<b>Construction:</b>
0.635	<b>Leadscrew Pitch (mm):</b>
5	<b>Load Capacity (kg):</b>
4.92 x 4.92	<b>Stage Size (inches):</b>
3	<b>Straight Line Accuracy (µm):</b>

**Hardware & Interface Connectivity**

English Micrometer	<b>Type of Drive:</b>
--------------------	-----------------------

**Threading & Mounting**

(21) 1/4-20, (4) 6-32, (8) 2-56	<b>Mounting Threads:</b>
---------------------------------	--------------------------

**Regulatory Compliance**

<b>Exempt</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<b>Contains SVHC(s)</b>	<b>REACH 241:</b>

**Product Details**

70mm and 125mm stages mount directly and do not require bottom adapter plates.

- Mechanically Compatible with our [TECHSPEC® Stages](#)
- Fine Micrometer Movement
- Locking Screw on Stages

Our newly developed precision TECHSPEC® Vertical Translations Stages (Z-axis stages) feature a unique and advanced crossed roller bearing guide system that provides high accuracy, rigidity and load capacity. Each stage is designed to integrate with our line of [TECHSPEC® stages](#) in order to provide flexibility in allowing the user to create a number of multi-axis configurations. These stages have a locking screw and fine micrometer movement. TECHSPEC® Vertical Translations Stages are constructed of aluminum and have a linear (Z) movement. The stages are available in both English and Metric versions and are offered in four sizes.

**Technical Information**

