

[See all 10 Products in Family](#)

12.5mm Square IR Cut-Off Filter



Stock #55-235 **20+ In Stock**

- 1 + **\$60^{.55}**

ADD TO CART

Volume Pricing	
Qty 1-24	\$60.55 each
Qty 25-49	\$54.25 each
Need More?	Request Quote

Product Downloads

General

IR Cut-Off Filter **Type:**

Physical & Mechanical Properties

12.5 x 12.5 **Dimensions (mm):**

12.50 **Length (mm):**

1.10 ±0.25 **Thickness (mm):**

12.50	Width (mm):
±0.25	Dimensional Tolerance (mm):
≥90	Clear Aperture (%):
Seamed	Edges:

Optical Properties

710.00	Cut-Off Wavelength (nm):
BOROFLOAT®	Substrate: <input type="checkbox"/>
Traditional Coated	Coating:
1.472	Index of Refraction (n_d):
80-50	Surface Quality:
Coating Specification: Surface 1: T=50% @ 710±30nm, T _{avg} >85% @ 480 - 680nm, T _{avg} <10% @ 740 - 1200nm Surface 2: N4 MgF ₂	
480 - 1200	Wavelength Range (nm):

Environmental & Durability Factors

<250	Operating Temperature (°C):
------	------------------------------------

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- 710nm Cut-Off Wavelength
- Circular and Rectangular Options
- Various Sizes Available

IR Cut-Off Filters are ideal for eliminating illumination beyond the visible spectrum in many visual and detector-based applications. These filters feature a 710nm cut-off wavelength. IR Cut-Off Filters are traditionally coated and have a BOROFLOAT® substrate. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass. IR Cut-Off Filters are available in circular and rectangular versions with various sizes for each.

Technical Information



[Quote Your Size](#)

[Compatible Mounts](#)

