

TECHSPEC® 12.7 x 25.4mm EFL 90° Protected Gold 100Å Off-Axis Parabolic Mirror



Stock **#35-485** 3-5 DAYS

[Other Coating Options](#)

- 1 + **S\$413.25**

ADD TO CART

Qty 1-5
S\$413.25
Qty 6+
S\$371.93
Volume Pricing
Request Quote

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
12.70 +0.00/-0.38

Effective Focal Length EFL (mm):
25.40

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 25.40
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 12.7
Surface Figure, RMS: λ/4
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 700 - 10000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #34-425
Substrate: Aluminum 6061-T6
Y Offset (mm): 25.4
Reflected Wavefront, RMS: λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant