

12.7mm Dia 20R/80T, UV-NIR Polka-Dot Beamsplitter



Stock #18-708 3-5 DAYS

⊖ 1 ⊕ **S\$210.25**

ADD TO CART

Qty 1-10

S\$210.25

Qty 11+

S\$178.71

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):
90

Coating:
Square Aluminum (AlMgF₂) Apertures

Construction:
Polka-Dot

Diameter (mm):
12.70

Dimensional Tolerance (mm):
+0.0/-0.5

Minimum Aperture (mm):
2.00

Operating Temperature (°C):
150 Maximum

Parallelism (arcmin):
<3

Reflection/Transmission Ratio (R/T):
20/80

Reflection/Transmission Tolerance (%):
±5 @ 45°

Substrate:
[Fused Silica](#) (Coming 7980)

Surface Quality:
80-50

Thickness (mm):
1.50 ±0.1

Type:
Standard Beamsplitter

Wavelength Range (nm):
250 - 2000

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
