


## 12.7mm Dia. 532nm 0°, Low Cost Laser Line Mirror



Stock **#38-618** 20+ In Stock

-

1

+

S\$147<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | S\$147.00 each                |
| Qty 11-49      | S\$133.70 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Laser Mrror

Physical & Mechanical Properties

Parallelism (arcmin):

<3

Clear Aperture (%):

>90

|                               |                                                       |
|-------------------------------|-------------------------------------------------------|
| 12.70 +0.0/-0.1               | Diameter (mm):                                        |
| 6.35 ±0.2                     | Thickness (mm):                                       |
| Optical Properties            |                                                       |
| 20-10                         | Surface Quality:                                      |
| 99                            | Reflection at DWL (%):                                |
| R <sub>abs</sub> >99% @ 532nm | Coating Specification:                                |
| λ/10                          | Surface Flatness (P-V):                               |
| Dielectric                    | Coating Type:                                         |
| Laser Mirror (532nm)          | Coating:                                              |
| 532                           | Design Wavelength DWL (nm):                           |
| 0                             | Angle of Incidence (°):                               |
| N-BK7                         | Substrate: <input type="checkbox"/>                   |
| 3 J/cm² @ 532nm, 20ns, 20Hz   | Damage Threshold, By Design: <input type="checkbox"/> |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| <a href="#">View</a>  | Certificate of Conformance: |

## Product Details

- >97% Reflectivity at Design Wavelength
- Up to λ/10 Surface Accuracy
- Excellent Cost to Performance Ratio
- Designs for Nd:YAG, Yb:YAG, and Diode Lasers

Low Cost Laser Line Mirrors are ideal for optical systems requiring cost-effective laser mirrors that do not compromise on performance. These mirrors feature N-BK7 or fused silica substrates, 20-10 surface quality, and up to λ/10 surface accuracy. With most mirrors providing >99% reflectance at their design wavelength, these mirrors are an ideal replacement for metallic coated mirrors in laser optical systems that require mirrors with higher reflectivity and higher laser damage thresholds. Low Cost Laser Line Mirrors are designed for either a 0° or 45° angle of incidence with coating options for Nd:YAG (266nm, 355nm, 532nm, 1064nm), Yb:YAG (515nm, 1030nm), or diode (488nm, 808nm, 850nm, 980nm) lasers.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide