


TECHSPEC[®] 12.7mm Dia x 100mm FL, VIS 0° Imaging Grade PCX Cylinder Lens



Stock **#34-650** 4 In Stock

-

1

+

S\$148⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$148.00 each
Qty 6-25	S\$133.00 each
Qty 26-49	S\$126.00 each
Need More?	Request Quote

Product Downloads

General

Type:
Cylinder Lens, Plano-Convex

Physical & Mechanical Properties

Diameter (mm):
12.70 +0.0/-0.025

	Bevel:
Protective as needed	
Center Thickness CT (mm):	2.00
Center Thickness Tolerance (mm):	±0.1
Clear Aperture CA (mm):	11.43
Edge Thickness ET (mm):	1.61

Optical Properties	
Effective Focal Length EFL (mm):	100.00
Substrate: ☐	N-BK7
f/#:	6.00
Numerical Aperture NA:	0.06
Coating:	VIS 0° (425-675nm)
Wavelength Range (nm):	425 - 675
Back Focal Length BFL (mm):	98.68
Coating Specification:	R _{avg} ≤0.4% @ 425 - 675nm
Radius R ₁ (mm):	51.68
Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4
Plano Axis Wedge (arcmin):	<5
Power Axis Wedge (arcmin):	<5

Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 235:	Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Beam Shaping Applications
- Tightly Controlled Optical and Geometric Tolerances
- Rectangular and Circular Form Factors Available

TECHSPEC® Imaging Grade PCXCylinder Lenses offer an ideal pairing of tightly controlled tolerances and scalable pricing for volume integration. As opposed to spherical lenses, which focus light in two dimensions, cylinder lenses are used to focus light in one dimension. AR Coating options are available for laser applications, minimizing stray light and maximizing throughput of a system. Our TECHSPEC Imaging Grade PCXCylinder Lenses are specified to control geometric characteristics in order to ensure consistent performance from design to manufacturing. Typical applications include circularizing elliptical beams from a laser diode, creating a light sheet for measurement systems, or projecting a laser line onto a surface.

Note: For negative focal length cylinder lenses, see our [TECHSPEC Imaging Grade PCV Cylinder Lenses](#).



Coating Curves

;