

12mm Dia. x 12mm FL Protected Aluminum, Concave Mirror



Stock #43-463 **7 In Stock**

- 1 + \$68⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-49	\$68.60 each
Qty 50-99	\$58.80 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

Diameter (mm):

12.00 ±0.50	Clear Aperture (%):
90	
3.0	Edge Thickness ET (mm):
±0.5	Thickness Tolerance (mm):
Optical Properties	
N-BK7	Substrate: <input type="checkbox"/>
±2	Focal Length Tolerance (%):
80-50	Surface Quality:
12.00	Effective Focal Length EFL (mm):
24.00	Radius of Curvature (mm):
f/1	Aperture (f/#):
Protected Aluminum (400-2000nm)	Coating:
R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm	Coating Specification:
Metal	Coating Type:
24.00	Radius R ₁ (mm):
400 - 2000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

TECHNICAL INFORMATION



