

12mm Dia. x 60mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-077** CLEARANCE **10 In Stock**

☐ [Other Coating Options](#)

-

1

+

S\$28^{.70}

ADD TO CART

Volume Pricing	
Qty 1+	S\$28.70 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex LensType:

Physical & Mechanical Properties

12.00 +0.00/-0.10Diameter (mm):

6.00Centering (arcmin):

1.41Edge Thickness ET (mm):


≥10.2	Clear Aperture CA (mm):
Optical Properties	
60.00	Effective Focal Length EFL (mm):
58.69	Back Focal Length BFL (mm):
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤1.75% @400 - 700nm	Coating Specification:
N-BK7	Substrate: ☐
±1	Focal Length Tolerance (%):
31.01	Radius R ₁ (mm):
5.00	f#:
0.10	Numerical Aperture NA:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Feature Standard Designs and Specifications
- Also Available [Uncoated](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. MgF₂ anti-reflection coating offers improved transmission in the visible spectrum. Commercial Grade MgF₂ Coated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information



Coating Curves