

TECHSPEC® 12mm Dia. x 9mm FL, Uncoated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock #21-222 **20+ In Stock**

⊖ 1 ⊕ **S\$134⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-24	S\$134.40 each
Qty 25-99	S\$102.20 each
Qty 100-249	S\$78.40 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

12.00 ±0.15

Diameter (mm):

10.00

Clear Aperture CA (mm):

2.51 **Edge Thickness ET (mm):**

5.60 ±0.20 **Center Thickness CT (mm):**

Protective as needed **Bevel:**

Convex **Shape of Back Surface:**

Optical Properties

9.00 @ 587.6nm **Effective Focal Length EFL (mm):**

0.67 **Numerical Aperture NA:**

5.57 **Back Focal Length BFL (mm):**

Zeonex K22R **Substrate:** □

587.6 **Aspheric Design Wavelength (nm):**

Uncoated **Coating:**

80-50 **Surface Quality:**

0.75 **f#:**

48.3 **Radius R₂ (mm):**

475 - 675 **Wavelength Range (nm):**

Infinite **Conjugate Distance:**

587.60 **Focal Length Specification Wavelength (nm):**

Environmental & Durability Factors

-30 to +70 **Operating Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details


- Color-Corrected Plastic Aspheres
- Diffractive Surface Minimizes Chromatic Aberration
- Low-Cost, Molded Design

TECHSPEC® Plastic Hybrid Aspheric Lenses are molded aspheric lenses with diffraction-limited designs that eliminate chromatic aberrations caused by broadband light sources. These hybrid aspheric lenses are ideal for imaging or ophthalmic applications, or for use with tunable lasers or broadband or multispectral illumination sources. The [aspheric lens](#) eliminates spherical aberration, while the diffractive surface features a negative optical dispersion to yield excellent color correction.

TECHSPEC Plastic Hybrid Aspheric Lenses are similar in performance, but offer several advantages to our [TECHSPEC Aspherized Achromatic Lenses](#). Hybrid aspheric lenses feature all-plastic, monolithic designs that are much lighter than comparable aspherized achromatic lenses. These optical lenses are also available in higher numerical apertures. However, plastic hybrid aspheric lenses are limited by the inherent diffraction efficiency of the aspheric surface, yielding lower overall transmission than comparable aspherized achromatic lenses.

These lenses won the 2011 Prism Award for Optics and Optical Components.

Technical Information



**Monochromatic Spot Size Comparison for
25mm Diameter f/1.2 Optical Components**

