


1.5" Diameter, Uncoated Plastic Acrylic Window



Stock **#71-541** 17 In Stock

-

1

+

S\$38^{.83}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$38.83 each
Qty 6-25	S\$30.99 each
Qty 26-49	S\$29.12 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Protective Window

Type:

Physical & Mechanical Properties

Protective as needed	Bevel:
34.29	Clear Aperture CA (mm):
38.10 ±2.54	Diameter (mm):
1.50 ±0.010	Diameter (inches):
1.52 ±0.08	Thickness (mm):
0.060 ±0.003	Thickness (inches):
Smooth, Machined	Edges:
Optical Properties	
58	Abbe Number (v _d):
Uncoated	Coating:
1.49	Index of Refraction (n _d):
PMMA	Substrate:
400 - 1600	Wavelength Range (nm):
Material Properties	
60	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Highly Scratch-Resistant
- High Visible Light Transmission
- Cost-Effective Alternative to Glass
- [Polycarbonate Plastic Windows](#) Also Available

Acrylic (PMMA) Plastic Windows are ideal for integration into lightweight optical systems. Compared to polycarbonate windows, acrylic windows are more scratch resistant and can be polished to restore optical quality but are more likely to chip or shatter. Acrylic (PMMA) Plastic Windows also provide a higher UV light transmission than polycarbonate and are recyclable. Acrylic windows are used in a wide variety of industrial and medical applications including aircraft windows, automobile headlights, and ophthalmological devices.

TECHNICAL INFORMATION

