

TECHSPEC<sup>®</sup> 150 x 150mm Linear Polarizer (XP42-70)



Stock #19-945 20+ In Stock

-

1

+

S\$99<sup>-40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | S\$99.40 each                 |
| Qty 11-25      | S\$82.32 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Linear Polarizer

Note:

Polarization axis can be identified as follows:  
Circular Parts - Parallel to direction of notch on polarizer  
Square Parts - Parallel to mark on protective film  
Rectangular Parts - Parallel to first listed dimension

Physical & Mechanical Properties

Dimensions (mm):

|                                                                       |                                             |
|-----------------------------------------------------------------------|---------------------------------------------|
| 150.0 x 150.0 +1.0/-1.0                                               |                                             |
| 0.72 ±0.1                                                             | Thickness (mm):                             |
| Polarizing Film on PMMA                                               | Construction:                               |
| Optical Properties                                                    |                                             |
| up to 9000:1 (nominal at 555nm)                                       | Extinction Ratio:                           |
| Polymer Film XP42-70                                                  | Substrate: <input type="checkbox"/>         |
| Single: 42 ±2<br>Parallel: 36.4<br>Crossed: <0.004 (nominal at 555nm) | Transmission (%):                           |
| 400 - 700                                                             | Wavelength Range (nm):                      |
| >99.98 (nominal at 555nm)                                             | Polarization Efficiency (%):                |
| <±5                                                                   | Transmission Variance after 1000 Hours (%): |
| Environmental & Durability Factors                                    |                                             |
| -10 to +60                                                            | Operating Temperature (°C):                 |
| ≤80% (no condensation)                                                | Operating Humidity:                         |
| Regulatory Compliance                                                 |                                             |
| Compliant                                                             | RoHS 2015:                                  |
| View                                                                  | Certificate of Conformance:                 |
| Compliant                                                             | Reach 235:                                  |

## Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available


Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

**Note:** Polarizer Film with adhesive available.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

## Technical Information





;