


[See all 6 Products in Family](#)

# 15mm Dia. Mirror, VIS Dielectric, Optotune Dual Axis Fast Steering Mirror with Position Feedback

See More by [Optotune](#)



Stock #73-043 [CONTACT US](#)

⊖ 1 ⊕ **\$4,137<sup>00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>\$4,137.00</b> each        |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

## General

**Note:**  
Do not connect or disconnect the mirror head while the base unit is connected to power as this will damage the mirror driver.

## Physical & Mechanical Properties

Step Response (μsec):

2 - 2.5

15.00

Diameter (mm):

8 (@ 10°)

Step Response 20° (ms):

±25

Mechanical Tilt (°):

30 - 100 RMS

Repeatability (µrad):

## Optical Properties

Dielectric Mirror (400-750nm)

Coating:

60-40

Surface Quality:

±25 (Mechanical) ±50 (Optical)

Scan Angle (°):

Ravg ≥98% @ 400 - 750nm

Coating Specification:

## Hardware & Interface Connectivity

24 - 48 VDC

Power Requirement:

Windows® 10

Operating System:

Power Supply Required and Sold Separately:  
USA: [#73-038](#)  
Europe: [#73-038](#)  
Japan: Not Available  
Korea: Not Available  
China: [#73-038](#)

Power Supply:

## Environmental & Durability Factors

0 to +40

Operating Temperature (°C):

-40 to +85

Storage Temperature (°C):

## Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 240:

## Product Details

- ±50° of Optical Scanning
- Protected Gold or Silver, and VIS Dielectric Coated Mirror Options
- Compact 45mm Diameter Housing Footprint
- Control via USB, SPI, or Analog Input

Optotune Fast Steering Mirrors provide a larger optical scanning range and mirror size than conventional galvanometers or micro-electro-mechanical (MEMS) mirrors. This dual axis voice-coil mirror (VCM) has a compact footprint with a large 15mm mirror that can be adjusted with ±25° of mechanical tilt for ±50° of optical scanning range. The mirror is operated using the [Optotune Cockpit GUI](#) via USB, serial peripheral interface (SPI), or analog input. Optotune Fast Steering Mirrors are available with a protected silver or gold, and VIS dielectric coating, enabling their use in both visible and near-infrared (NIR) applications. Typical applications for these fast steering mirrors include automotive LiDAR, biometric eye tracking, and field of view expansion of vision systems.

**Note:** [#14-574](#), [#14-575](#), and [#18-281](#) require [#14-576](#) for operation and [#73-039](#), [#73-042](#), and [#73-043](#) require [#73-038](#) for operation. A heatsink is included with each mirror and recommended to be used to ensure proper heat-dissipation. Do not connect or disconnect the mirror head while the base unit is connected to power as this will damage the mirror driver.