


[See all 109 Products in Family](#)

**TECHSPEC® 15mm Dia 0.38 NA, UV-VIS Coated, UV Fused Silica Aspheric Lens**



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#84-336** **4 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **S\$768<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$768.60</b> each
Qty 6-10	<b>S\$691.60</b> each
Qty 11-25	<b>S\$645.40</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

**Diameter (mm):**

15.00 +0.0/-0.1	<b>Centering (arcmin):</b>
≤5	
13.5	<b>Clear Aperture CA (mm):</b>
2.68	<b>Edge Thickness ET (mm):</b>
6.00 ±0.1	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
Plano	<b>Shape of Back Surface:</b>

## Optical Properties

20.00 @ 587.6nm	<b>Effective Focal Length EFL (mm):</b>
0.38	<b>Numerical Aperture NA:</b>
15.89	<b>Back Focal Length BFL (mm):</b>
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
587.6	<b>Aspheric Design Wavelength (nm):</b>
1.2λ	<b>Asphere Figure Error, RMS @ 632.8nm:</b>
UV-VIS (250-700nm)	<b>Coating:</b>
R <sub>avg</sub> <2.5% @ 250 - 700nm	<b>Coating Specification:</b>
60-40	<b>Surface Quality:</b>
1.33	<b>f#:</b>
250 - 700	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
50.00	<b>Power (diopters):</b>

## Regulatory Compliance


<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 235:</b>


## Product Details

- Low Coefficient of Thermal Expansion
- Precision and High Precision Options
- High Numerical Apertures to Maximize Throughput

TECHSPEC® UV Fused Silica Aspheric Lenses offer the benefits of an aspheric element combined with the manufacturing precision of state-of-the-art grinding and polishing equipment. These fused silica optics can be easily designed and integrated into complex optical systems with the available prescription data. Featuring low f#’s, which allow for a larger aperture and thus more light gathering and focusing performance, these fused silica lenses are computer-optimized to eliminate spherical and minimize higher order aberrations. TECHSPEC® UV Fused Silica Aspheric Lenses offer a low coefficient of thermal expansion, making them ideal for applications in metrology, beam-focusing or collimating, and OEM integration. These lenses are available in a variety of coating options and are offered in sizes ranging from 10-50mm.

## Technical Information





## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---