

TECHSPEC[®] 15mm Dia 0.60 NA, 355nm V-Coat, Aspheric Lens



TECHSPEC[®] Laser Line Coated Aspheric Lenses

Stock **#33-009** **9 In Stock**

☐ [Other Coating Options](#)

-

1

+

S\$761⁶⁹

ADD TO CART

Volume Pricing	
Qty 1-5	S\$761.69 each
Qty 6-25	S\$612.34 each
Qty 26-49	S\$575.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Aspheric Lens

Type:

Physical & Mechanical Properties	
15.00 +0.0/-0.1	Diameter (mm):
≤5	Centering (arcmin):
13.5	Clear Aperture CA (mm):
2.47	Edge Thickness ET (mm):
9.00 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:
Optical Properties	
12.50 @ 587.6nm	Effective Focal Length EFL (mm):
0.60	Numerical Aperture NA:
6.33	Back Focal Length BFL (mm):
Fused Silica (Corning 7980)	Substrate: □
355	Aspheric Design Wavelength (nm):
1.2λ	Asphere Figure Error, RMS @ 632.8nm:
Laser V-Coat (355nm)	Coating:
R _{abs} <0.25% @ 355nm	Coating Specification:
60-40	Surface Quality:
0.83	f/#:
Infinite	Conjugate Distance:
7.5 J/cm ² @ 355nm, 20ns, 20Hz	Damage Threshold, By Design: □
80.00	Power (diopters):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Designed and Coated for Nd:YAG Laser Wavelengths
- High Laser Damage Thresholds
- Low Coefficient of Thermal Expansion

TECHSPEC® Laser Line Coated Aspheric Lenses are designed to maximize performance in high power Nd:YAG laser applications. The aspheric designs minimize spherical aberration to decrease laser spot size and maintain high power per area. Additionally, TECHSPEC® Laser Line Coated Aspheric Lenses feature high performance coatings that have been optimized for the most popular Nd:YAG laser wavelengths and a high damage threshold, UV fused silica substrate that is highly resistant to thermal expansion.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more

- High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS

