


15mm Dia. NIR Linear Polarizing Film



Stock #18-938 CLEARANCE 8 In Stock

-

1

+

S\$84^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$84.00 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer

Type:

Protective Film on Both Sides

Note:

Physical & Mechanical Properties

15.00

Diameter (mm):

0.50 ±0.1

Thickness (mm):

Dimensional Tolerance (mm):

±0.25	
Polarizing Film	Construction:
Optical Properties	
Uncoated	Coating:
400:1 (Average @ 800 - 2200nm)	Extinction Ratio:
Polymer Film on TAC	Substrate: □
Single: 29 (400 - 760 nm), 39 (761 - 2200nm) Crossed: 0.02 (400 - 760nm), 0.11 (761 - 2200nm)	Transmission (%):
400 - 2200	Wavelength Range (nm):
99.83 @ 400 - 760nm 99.63 @ 761 - 2200nm	Polarization Efficiency (%):
29 @ 400 - 760nm 39 @ 761 - 2200nm	Transmission, Single (%):
0.02 @ 400 - 760nm 0.11 @ 761 - 2200nm	Transmission, Crossed (%):
Environmental & Durability Factors	
Heat Resistance 85°C Dry Cold Resistance -55°C	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Ideal for NIR Polarization Applications
- >400:1 Extinction Ratio from 800 - 2200nm
- High Efficiency Across Wavelength Range
- Durable Polymer Substrate

Near-Infrared (NIR) Linear Polarizing Film consists of a durable polymer substrate and is ideal for imaging applications that range from the visible to NIR (400 - 2200nm). This polarizing polymer film features an excellent average transmission of 39% with greater than 99.6% polarization efficiency for incident randomly polarized light between 760 and 2200nm. Multiple rectangular sizes are available to accommodate light sources that range from low power NIR lasers with small beam diameters, to larger LED light beams. Near-Infrared (NIR) Linear Polarizing Film is used in industrial imaging and laboratory applications, i.e. to attenuate the intensity of low output NIR lasers and LEDs or to reduce glare in images recorded using NIR photodetectors. The polarization axis is labelled on the protective masking of the polarizing polymer film for rectangular parts and as a notch cutout on the polarizing polymer film for circular parts.

Note: Remove protective masking before first use.

Technical Information

