

[See all 6 Products in Family](#)

15mm Dia. Mirror, Protected Silver, Optotune Dual Axis Fast Steering Mirror with Position Feedback

See More by [Optotune](#)



Stock **#14-574** CLEARANCE CONTACT US

-

1

+

S\$4,326⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$4,326.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

MR-15-30-PS-25x25D

Model Number:

Note:

Do not connect or disconnect the mirror head while the base unit is connected to power as this will

damage the mirror driver.

Physical & Mechanical Properties

15.00	Diameter (mm):
2	Step Response 0.1° (ms):
12	Step Response 20° (ms):
45	Housing Diameter (mm):
±25	Mechanical Tilt (°):
30 - 100 RMS	Repeatability (µrad):

Optical Properties

Protected Silver	Coating:
60-40	Surface Quality:
±25 (Mechanical) ±50 (Optical)	Scan Angle (°):
R _{avg} >94% @400 - 2000nm	Coating Specification:

Hardware & Interface Connectivity

15 - 28 VDC	Power Requirement:
Windows® 10	Operating System:
Power Supply: Power Supply Required and Sold Separately. USA: #14-576 Europe: #14-576 Japan: Not Available Korea: Not Available China: #14-576	

Environmental & Durability Factors

0 to +40	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- ±50° of Optical Scanning
- Protected Gold or Silver, and VS Dielectric Coated Mirror Options
- Compact 45mm Diameter Housing Footprint
- Control via USB, SPI, or Analog Input

Optotune Fast Steering Mirrors provide a larger optical scanning range and mirror size than conventional galvanometers or micro-electro-mechanical (MEMS) mirrors. This dual axis voice-coil mirror (VCM) has a compact footprint with a large 15mm mirror that can be adjusted with ±25° of mechanical tilt for ±50° of optical scanning range. The mirror is operated using the [Optotune Cockpit GUI](#) via USB, serial peripheral interface (SPI), or analog input. Optotune Fast Steering Mirrors are available with a protected silver or gold, and VS dielectric coating, enabling their use in both visible and near-infrared (NIR) applications. Typical applications for these fast steering mirrors include automotive LiDAR, biometric eye tracking, and field of view expansion of vision systems.

Note: [#14-574](#), [#14-575](#), and [#18-281](#) require [#14-576](#) for operation and [#73-039](#), [#73-042](#), and [#73-043](#) require [#73-038](#) for operation. A heatsink is included with each mirror and recommended to be used to ensure proper heat-dissipation. Do not connect or disconnect the mirror head while the base unit is connected to power as this will damage the mirror driver.