

1" Travel, Eng Micrometer, Solid Top 1.75" Stage



Stock #53-856 **2 In Stock**

⊖ 1 ⊕ \$1,925.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	\$1,925.00 each
Need More?	Request Quote

Product Downloads

General

English **Type:**
Solid Top **Note:**

Physical & Mechanical Properties

Linear (X) **Type of Movement:**
Ball Bearing **Guide System:**
Drive Orientation:

Center Drive

44.4 x 44.4

Stage Size (mm):

Travel (inches):

1

Construction:

Aluminum Top and Base/440C Stainless Steel Bearings

Graduation (inches):

0.00005

Load Capacity, Normal (lbs):

25

Load Capacity, T_a (lbs):

10

Load Capacity, T_b (lbs):

5

Stage Size (inches):

1.75 x 1.75

Straight Line Accuracy (inches):

0.00008 per inch of travel

Weight (lbs):

1.0

Hardware & Interface Connectivity

Type of Drive:

Digital Micrometer (English)

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Product Details

- 0.001mm Resolution Directly Readable Micrometer
- Readout in Inches or Millimeters
- Available with English or Metric Mounting Holes

Available with standard (English) or metric mounting holes, these digital micrometers have a precision ground mounting surface and clear LCD readout. The micrometers also feature incremental or absolute positional modes, zero set at any position, inch or millimeter readouts (0.001mm resolution), display hold, and automatic shutdown to conserve the integral battery. Stage travels are one inch and table tops are available with or without a thru-hole.

Technical Information

Figure	Size A	Size B	Size C	Size D	Size E	Size F	Threading G	Threading H	Stock No.
Solid Top									
A	1.75"	0.75"	1.12"	2.12"	1.00"	0.50"	6-32	#6	#53-857
A	1.75"	0.75"	1.12"	2.12"	1.00"	—	6-32	#6	#53-856
A	2.62"	1.00"	2.00"	3.00"	2.00"	—	10-32	#1/4	#38-199
A	2.62"	1.00"	2.00"	3.00"	2.00"	1.00"	10-32	#1/4	#38-203
B	5.00"	1.00"	4.00"	—	4.00"	—	1/4-20	#1/4	#38-202
B	5.00"	1.00"	4.00"	—	4.00"	2.00"	1/4-20	#1/4	#38-204
C	44.4mm	19.0mm	30.0mm	53.8mm	25.0mm	—	M4	M4	#55-461
C	66.5mm	25.4mm	50.0mm	75.9mm	50.0mm	—	M5	M6	#55-462
D	127.0mm	25.4mm	100.0mm	—	—	—	M6	M6	#55-463
D	66.5mm	25.4mm	50.0mm	75.9mm	50.0mm	25.4mm	M5	M6	#55-464

