

[See all 130 Products in Family](#)

**TECHSPEC® 19.1mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror**



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#34-814** **8 In Stock**

⊖ 1 ⊕ **S\$224<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$224.00</b> each
Qty 6-25	<b>S\$198.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

**Back Surface:**

Commercial Polish

19.10 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.20 **Thickness (mm):**

## Optical Properties

10-5 **Surface Quality:**

99.5 **Reflection at DWL (%):**

**Coating Specification:**  
R<sub>abs</sub> >99.5% @ 266nm  
R<sub>avg</sub> >99.5% @ 263 - 268nm

263 - 268 **Wavelength Range (nm):**

λ/10 **Surface Flatness (P-V):**

Dielectric **Coating Type:**

Laser Mirror (263-268nm) **Coating:**

266 **Design Wavelength DWL (nm):**

45 **Angle of Incidence (°):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

**Damage Threshold, Reference:**   
2.5 J/cm<sup>2</sup> @ 266nm, 20ns, 20Hz

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

**Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts