

[See all 18 Products in Family](#)

## 19.1mm Dia., 10 Arcsec, Bare Gold Replicated Hollow Metal Retroreflector



Replicated Hollow Metal Retroreflectors

Stock **#15-900** **4 In Stock**

⊖ 1 ⊕ **\$630<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-9	<b>\$630.00</b> each
Qty 10-24	<b>\$585.90</b> each
Qty 25+	<b>\$535.50</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Retroreflector **Type:**  
Standard Profile **Style:**

#### Physical & Mechanical Properties

16.51 **Clear Aperture CA (mm):**

19.10 Diameter (mm):

26.17 Height (mm):

+0.025/-0.051 Dimensional Tolerance (mm):

## Optical Properties

10 Beam Deviation (arcsec):

Bare Gold Coating:

Aluminum Substrate:

60-40 Surface Quality:

Left-Handed Image Orientation:

Coating Specification:  
R<sub>avg</sub> >94% @ 700 - 800nm  
R<sub>avg</sub> >97% @ 800 - 2000nm  
R<sub>avg</sub> >98% @ 2 - 12μm

180 Ray Deviation (°):

700 - 12000 Wavelength Range (nm):

## Threading & Mounting

10-24 Mounting Threads:

## Regulatory Compliance



[View](#) Certificate of Conformance:

## Product Details

- Monolithic Aluminum Construction
- Return Beam Accuracy Unaffected by Vibration
- Bare Gold or Enhanced Aluminum Coating Options
- Low Profile Versions are Available

Replicated Hollow Metal Retroreflectors feature a monolithic aluminum construction and an integrated mount to provide return beam performance unaffected by vibration. These retroreflectors are offered with bare gold coatings applied to the first surface, maximizing their reflectivity in the infrared (IR), or enhanced aluminum coatings for optimal performance in the visible spectrum. Designed to have the entirety of their optical path in air, these retroreflectors do not require antireflection coatings for optimal performance and can be used over wider wavelength ranges than glass retroreflectors. Replicated Hollow Metal Retroreflectors are ideal for applications where an optical path through a glass prism is undesired, reduced weight is required, or where high shock and vibration levels are expected. The replication manufacturing process of these optics enables cost-effective designs while providing high performance beam return accuracy.

## Technical Information



REPLICATED HOLLOW METAL RETROREFLECTORS					
Diameter (mm)	Height (mm)	Mounting Threads	Coating	Stock No.	
				5 Arcseconds	10 Arcseconds
12.7	21.68	10-24	Bare Gold	#15-897	#15-898
19.1	26.17	10-24	Bare Gold	#15-899	#15-900
25.4	30.66	10-24	Bare Gold	#15-901	#15-902
38.1	39.64	10-24	Bare Gold	#15-903	#15-904

LOW PROFILE REPLICATED HOLLOW METAL RETROREFLECTORS						
Dimension A (mm)	Dimension B (mm)	Dimension C (mm)	Coating	Stock No.		
				2 Arcseconds	5 Arcseconds	10 Arcseconds
12.7	8.63	12.8	Bare Gold	N/A	#23-854	#23-855
25.4	21.69	20.32	Bare Gold	#23-856	#23-857	#23-858