

TECHSPEC®

200 x 200mm Linear Polarizing Film (XP42-18)



Stock #86-181 CLEARANCE 3-5 DAYS

-

1

+

S\$109.43

ADD TO CART

Qty 1+

S\$109.43

Volume Pricing

[Request Quote](#)

Get Product Downloads

Extinction Ratio:
9000:1 (nominal at 555nm)

Substrate: [Polymer Film XP42-18](#)

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
200.0 x200.0

Thickness (mm):
0.19 ±0.03

Transmission (%) : Single: 42 Parallel: 36 Crossed: <0.004 (nominal at 555nm)
Type : Linear Polarizer
Dimensional Tolerance (mm) : ±2.0
Construction : Polarizing Film
Note : Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.98 (nominal at 555nm)
Heat Resistance (°C x Hours) : 80 x 500
#Sorting : 16.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Contains SVHC(s)