

2 - 5.5um InAsSb Photovoltaic Multi-Juncton IR Detector, PVMA-1TE-5-1x1-TO39-pSiAR-70



2 - 5.5um InAsSb Photovoltaic Multi-Juncton IR Detector, PVMA-1TE-5-1x1-TO39-pSiAR-70

Stock #90-461 NEW 2 In Stock

-

1

+

S\$560⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$560.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
IR Photovoltaic Detector	Type:
PVMA-1TE-5-1x1-TO39-pSiAR-70	Model Number:
TO-39	Package:
Vigo Photonics	Manufacturer:

Physical & Mechanical Properties	
7	Weight (g):
1.00 x 1.00	Active Area (mm):
Optical Properties	
2000 - 5500	Spectral Response (nm):
70	Acceptance Angle (°):
Environmental & Durability Factors	
-20 to +70	Operating Temperature (°C):
-20 to +85	Storage Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Mid and Long-Wave Infrared (MMIR/LWIR) Spectral Range
- 1 × 1mm² Active Areas with Acceptance Angles up to 90°
- TO-39 and TO-8 Package Styles with Specialized Anti-Reflection Windows

Vigo Photonics Infrared Detectors deliver high-performance mid and long-wave IR detection with exceptional sensitivity and stability across demanding applications. These HgCdTe and InAsSb detectors are available with a variety of cooling configurations, including single, dual, triple, and quad-stage thermoelectric coolers, to optimize signal-to-noise ratios. Models are offered with active areas of 1 × 1mm² and acceptance angles up to 90°, providing flexibility for system integration. Vigo Photonics Infrared Detectors feature precision packaging options such as TO-39 and TO-8 housings with specialized anti-reflection coatings for maximum throughput. These detectors combine reliability with infrared technology, making them ideal for spectroscopy, gas analysis, and defense applications.