

## 200 x 200mm 220 Grit Ground Glass Diffuser



Stock #47-952 **16 In Stock**

⊖ 1 ⊕ S\$118<sup>.30</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>S\$118.30</b> each
Qty 11+	<b>S\$106.40</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Ground Glass Diffuser **Type:**

Sandblasted on first surface **Note:**

#### Physical & Mechanical Properties

±0.76 **Dimensional Tolerance (mm):**

200.00 x 200.00 **Dimensions (mm):**

Seamed	<b>Edges:</b>
220	<b>Grit:</b> <input type="checkbox"/>
1.60	<b>Thickness (mm):</b>
200.00	<b>Width (mm):</b>
200.00	<b>Length (mm):</b>

### Optical Properties

Uncoated	<b>Coating:</b>
Float Glass	<b>Substrate:</b> <input type="checkbox"/>
350 - 2000	<b>Wavelength Range (nm):</b>

### Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

### Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

### Technical Information



### Quote Your Size